

760255048 | PPL-SP-16LC-SM-PT-BEU



Propel Singlemode Splice Cassette, 16LC/UPC with internal shutters, 250 μ m OS2 single fiber pigtails, Method B Enhanced ULL

- Can be installed and removed from front or rear of panel
- This component requires 4 of the 12 lanes on the Propel Panel blade

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	SYSTIMAX®
Product Type	Fiber cassette with pigtails
Product Brand	Propel
Product Series	PPL

General Specifications

Color, front	Blue
Interface, front	LC/UPC
Interface, rear	Ribbon pigtail
Polarity	Method B Enhanced (ULL)
Shuttered	Yes
Total Fibers, quantity	16

Dimensions

Height	67.31 mm 2.65 in
Width	131.013 mm 5.158 in

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A2
Insertion Loss, maximum	0.25 dB

Environmental Specifications

Qualification Standards	IEC 61753-1 TIA-568.3-D
--------------------------------	---------------------------

760255048 | PPL-SP-16LC-SM-PT-BEU

Safety Standard UL

Packaging and Weights

Included Mass Fusion Splice Protection Sleeves

Packaging quantity 1

Included Products

103897-000 – SMOUV Fiber Optic Splice Heat Shrink Protective Sleeve for FIST Trays, pack of 100
SMOUV-1120-02 pcs