

# GROUNDING-SERIES

---

## Base Product



## Standard and Universal Grounding Kit Series

### Product Classification

<b>Product Type</b>	Grounding kit
<b>Product Brand</b>	HELIAX®

### General Specifications

<b>Bonding Conductor Jacketing Material</b>	PVC
<b>Bonding Conductor Material</b>	Copper
<b>Color</b>	Black

### Electrical Specifications

<b>Current Handling Test Method</b>	MIL-STD-1757
<b>Grounding, Bonding and Shielding Test Method</b>	MIL-STD-188-124A
<b>Lightning Protection Test Method</b>	IEC 1024-1

### Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)
<b>Storage Temperature</b>	-40 °C to +80 °C (-40 °F to +176 °F)
<b>Blowing Rain Test Method</b>	MIL-STD-810, Method 506
<b>Corrosion Test Method</b>	MIL-STD-1344, Method 1001
<b>Freezing Rain/Icing Test Method</b>	MIL-STD-810, Method 521
<b>Humidity Test Method</b>	MIL-STD-1344, Method 1002
<b>Immersion Test Method</b>	IEC 60529:2001, IP68
<b>UV Resistance Test Method</b>	MIL-STD-810, Method 505
<b>Vibration Test Method</b>	MIL-STD-202, Method 214
<b>Weatherproofing Method</b>	Butyl and electric tape

# GROUNDING-SERIES

---

\* Footnotes

**Grounding, Bonding and Shielding Test Method** Military Standard for Grounding, Bonding, and Shielding: Bond Resistance Requirement of a Maximum dc resistance of 0.001 ohm

**Lightning Protection Test Method** Protection Against Lightning Electromagnetic Impulse, Table 1—Protection Level III–IV, 1995-02