

# RR-RM1560

## Six Sector Ring Mount Kit



- Ring Mount for the attachment of radios and other equipment to the tower face.
- Designed to be a single connection point to the tower reducing costs associated with adding connection points to the tower.
- Allows for up to (6) mounting pipes.
- Accommodates 2-3/8" or 2-7/8" pipes
- Mast pipes & U-bolts ordered separate
- For 2-3/8" pipes use (2) "GUB-4240" per pipe
- For 2-7/8" pipes use (2) "GUB-4350" per pipe
- Pole range of 15" to 60" diameter

### Product Classification

Product Type	Universal ring mount
Ordering Note	ANDREW® standard product with terms
Warranty	One year

### General Specifications

Mounting	Monopole, 381–1524 mm (15–60 in) OD
Pipe, quantity	0
Sectors, quantity	6

### Dimensions

Height	254 mm   10 in
Length	152.4 mm   6 in
Mounting Diameter, maximum	1524 mm   60 in
Mounting Diameter, minimum	381 mm   15 in
Pipe Outer Diameter	0 mm   0 in
Mounting Circumference, maximum	4,785.36 mm   188.4 in
Mounting Circumference, minimum	1,196.34 mm   47.1 in

# RR-RM1560

## Material Specifications

**Material Type** Hot dip galvanized steel

## Packaging and Weights

**Included** Hardware | Mount

**Packaging quantity** 1

**Weight, net** 55.52 kg | 122.4 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.andrew.com/ProductCompliance">www.andrew.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



## \* Footnotes

**Warranty** For more information, please consult our Product Warranty guidelines