

SFG22-14-4-96

Mechanical Specifications

| | |
|--|--|
| Load Capacity | With additional stiff arm at 300 ft AGL: 600 lb per pipe w/out ice / 1275 lb per pipe including ice |
| Wind Rating | For Specifications, please contact steelproducts@commscope.com or call 800-255-1479 |
| Wind Rating Test Method | TIA/EIA-222-G |
| Wind Rating with Additional Stiff Arm | 300 ft AGL: 120 mph (BWS) without ice /60 mph with ice |

Environmental Specifications

| | |
|---|---|
| EPA with 1/2 in (12 mm) radial ice | 1.449 m ² 15.6 ft ² |
| EPA without ice | 1.059 m ² 11.4 ft ² |

Packaging and Weights

| | |
|---------------------------|--|
| Included | Frame Pipe mounts Plain end pipes (4) Stiff arm Tower attachment |
| Packaging quantity | 1 |
| Weight, net | 240.132 kg 529.4 lb |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Above maximum concentration value |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| ROHS | Compliant/Exempted |
| UK-ROHS | Compliant |



* Footnotes

| | |
|--|--|
| Wind Rating | BWS—Base Wind Speed; FBC—Florida Building Code |
| Wind Rating with Additional Stiff Arm | BWS—Base Wind Speed; FBC—Florida Building Code |
| EPA with 1/2 in (12 mm) radial ice | EPA—Effective Projected Area |
| EPA without ice | EPA—Effective Projected Area |