


TF-M3S-20



Tower Face Mount with dual 20 ft x 3-1/2 in OD face pipe supports, includes pipe

Product Classification

Product Type Tower face mount

General Specifications

Mounting Angle 60°, 203.2 mm (8 in) | Angle 90°, 152.4 mm (6 in) | Straight or tapered legs up to 203.2 mm (8 in) OD

Pipe, quantity 1

Tower Taper Non-tapered | Tapered

Dimensions

Height 63 in | 1,600.2 mm

Face Width 20 ft | 6.096 m

Width 240 in | 6,096 mm

Length 12 in | 304.8 mm

Pipe Length 63 in | 1,600.2 mm

Face Support Pipe Diameter 3.5 in | 88.9 mm

Mounting Diameter, maximum 8 in | 203.2 mm

Mounting Diameter, minimum 0 in | 0 mm

Pipe Outer Diameter 4.5 in | 114.3 mm

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating 120 mph (BWS) at 100 ft AGL

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

TF-M3S-20

Included	Crossover plates Pipes Saddle mounts
Packaging quantity	1
Weight, net	647.5 lb 293.701 kg

* Footnotes

Wind Rating	BWS—Base Wind Speed; FBC—Florida Building Code
--------------------	--