

F2A-HMHM-10M-P



FSJ2-50 SureFlex® Jumper with interface types 4.3-10 Male and 4.3-10 Male ,10 m

- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

Product Classification

Product Type	SureFlex® Premium, static PIM
Product Brand	HELIAX® SureFlex®
Product Series	FSJ2-50

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	4.3-10 Male
Interface, Connector B	4.3-10 Male
Specification Sheet Revision Level	A

Dimensions

Length	10 m 32.808 ft
Nominal Size	3/8 in

Electrical Specifications

3rd Order IMD Static	-110 dBm
3rd Order IMD Static Test Method	Two +43 dBm carriers

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.101	26.4
1700–2200 MHz	1.101	26.4
2500–2700 MHz	1.101	26.4

Jumper Assembly Sample Label

F2A-HMHM-10M-P



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition