

TP-G300-B



Universal Tripod Base Kit for 2-7/8 in - 3-1/2 in OD pipes

Product Classification

Product Type Tripod mount

General Specifications

Mounting Non-penetrating | Surfaces

Pipe, quantity 0

Dimensions

Height 838.2 mm | 33 in

Width 1524 mm | 60 in

Length 1.524 m | 5 ft

Pipe Length 0 mm | 0 in

Pipe Outer Diameter 73.66 mm | 2.9 in | 88.9 mm | 3.5 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating 85 mph (BWS) at 100 ft AGL using Exposure C per UBC

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included Mount, with or without pipe

Packaging quantity 1

Weight, net 51.8 kg | 114.199 lb

TP-G300-B

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

ISO 9001:2015

ROHS

UK-ROHS

Classification

Above maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant/Exempted

Compliant



* Footnotes

Wind Rating

BWS—Base Wind Speed; FBC—Florida Building Code