

L5-CLAMP-3B



KwikClamp™ Hanger for 7/8 in coaxial cable, triple stack; includes hardware

Product Classification

| | |
|----------------------|--|
| Product Type | Hanger kit |
| Product Brand | KwikClamp™ |
| Ordering Note | CommScope® standard product in Europe, the Middle East, and Africa |

General Specifications

| | |
|--------------------------|---|
| Cables per Hanger | 1 |
| Color | Black |
| Hanger Type | KwikClamp™ hanger |
| Mounting | 3–25 mm flat plate Round Member 8-25 mm |

Dimensions

| | |
|-------------------------------------|--------------------|
| Maximum Stack Height | 3 |
| Height | 197 mm 7.756 in |
| Width | 45 mm 1.772 in |
| Length | 32 mm 1.26 in |
| Compatible Diameter, maximum | 28.2 mm 1.11 in |
| Compatible Diameter, minimum | 26.7 mm 1.051 in |
| Nominal Size | 7/8 in |
| Hanger Spacing, maximum | 1.83 m 6.004 ft |

Electrical Specifications

| | |
|------------------------------------|--------|
| Return Loss Effect, maximum | 0.1 dB |
| DTF Effect, maximum | 0.1 dB |

L5-CLAMP-3B

Material Specifications

Material Type Engineered plastic | Stainless steel

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Corrosion Resistance, minimum with no degradation ≥500 hours in salt spray chamber

Environmental Strength Capability Five times cable weight

UV Resistance, minimum with no degradation ≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed 15.5 cm | 6.102 in

Width, packed 30.5 cm | 12.008 in

Length, packed 35.5 cm | 13.976 in

Included Hardware

Packaging quantity 24

Weight, gross 5.53 kg | 12.192 lb

Regulatory Compliance/Certifications

| Agency | Classification |
|------------|--|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power