


# 760257311 | UNJ600-RD



M-Series Modular Jack, RJ45, Cat6 Unshielded, Red

## Product Classification

<b>Regional Availability</b>	North America
<b>Portfolio</b>	Uniprise®
<b>Product Type</b>	Modular jack
<b>Product Series</b>	UNJ Series

## General Specifications

<b>ANSI/TIA Category</b>	6
<b>Cable Type</b>	Unshielded
<b>Color</b>	Red
<b>Conductor Type</b>	Solid   Stranded
<b>Integrated Dust Cover Type</b>	None
<b>Mounting</b>	M Series faceplates and panels
<b>Outlet Feature</b>	Inverted jack face
<b>Outlet Type</b>	Standard
<b>Termination Tool</b>	SL Termination tool
<b>Termination Type</b>	IDC
<b>Transmission Standards</b>	ANSI/TIA-568-C.2   ISO/IEC 11801 Class E
<b>Wiring</b>	T568A   T568B

## Dimensions

<b>Panel Thickness, recommended</b>	1.6 mm   0.063 in
<b>Compatible Insulated Conductor Diameter, maximum</b>	1.45 mm   0.057 in
<b>Contact Plating Thickness</b>	1.27 µm
<b>Compatible Conductor Gauge, solid</b>	24–22 AWG
<b>Compatible Conductor Gauge, stranded</b>	26–24 AWG

## Electrical Specifications

# 760257311 | UNJ600-RD

---

## Remote Powering

Fully supports the safe delivery of power over LAN cabling described by IEEE 802.3bt (Type 4) and complies with the unmating under electrical load requirements prescribed by IEC 60512-99-002

## PoE Durability

Supports IEEE 802.3bt Type 4 (90 W) applications greater than 3000 plug to jack mating cycles

## Material Specifications

### Contact Base Material

Beryllium copper

### Contact Plating Material

Gold

### Material Type

PC+ABS

## Mechanical Specifications

### Plug to Jack Mating Cycles

Complies to IEC 60603-7 series

## Environmental Specifications

### Operating Temperature

-10 °C to +60 °C (+14 °F to +140 °F)

### Storage Temperature

-40 °C to +70 °C (-40 °F to +158 °F)

### Flammability Rating

UL 94 V-0

## Packaging and Weights

### Packaging quantity

1

### Packaging Type

Bag

## Regulatory Compliance/Certifications

### Agency

### Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant

