

RVV-65B-R3VB-V2

6-port sector antenna, 2x 694-960 and 4x 1695-2690 MHz, 65° HPBW, 3x RET

- All Internal RET actuators are connected in “Cascaded SRET” configuration
- Retractable tilt indicator rods
- Uses the 4.3-10 connector which is 40 percent smaller than the 7-16 DIN connector

General Specifications

Antenna Type	Sector
Band	Multiband
Color	Light Gray (RAL 7035)
Grounding Type	RF connector inner conductor and body grounded to reflector and mounting bracket
Performance Note	Outdoor usage
Radome Material	Fiberglass, UV resistant
Radiator Material	Low loss circuit board
Reflector Material	Aluminum
RF Connector Interface	4.3-10 Female
RF Connector Location	Bottom
RF Connector Quantity, mid band	4
RF Connector Quantity, low band	2
RF Connector Quantity, total	6

Remote Electrical Tilt (RET) Information

RET Hardware	CommRET v2
RET Interface	8-pin DIN Female 8-pin DIN Male
RET Interface, quantity	1 female 1 male
Input Voltage	10-30 Vdc
Internal RET	Low band (1) Mid band (2)
Power Consumption, active state, maximum	10 W
Power Consumption, idle state, maximum	2 W
Protocol	3GPP/AISG 2.0 (Single RET)

Dimensions

RVV-65B-R3VB-V2

Width	397 mm 15.63 in
Depth	157 mm 6.181 in
Length	1997 mm 78.622 in
Net Weight, antenna only	19.5 kg 42.99 lb

Electrical Specifications

Impedance	50 ohm
Operating Frequency Band	1695 – 2690 MHz 694 – 960 MHz
Polarization	±45°
Total Input Power, maximum	800 W

Electrical Specifications

	R1	R1	R1	Y1,Y2	Y1,Y2	Y1,Y2	Y1,Y2
Frequency Band, MHz	698–806	790–894	890–960	1695–1995	1920–2300	2300–2500	2490–2690
RF Port	1,2	1,2	1,2	3-6	3-6	3-6	3-6
Gain, dBi	16.1	16.4	16.4	18.4	18.9	18.7	19.2
Beamwidth, Horizontal, degrees	61	59	64	59	58	58	58
Beamwidth, Vertical, degrees	12.1	10.9	10	6.2	5.6	5	4.7
Beam Tilt, degrees	2–14	2–14	2–14	2–12	2–12	2–12	2–12
USLS (First Lobe), dB	20	20	19	17	20	20	22
Front-to-Back Ratio, Copolarization 180° ± 30°, dB	29	30	31	31	31	29	29
Isolation, Cross Polarization, dB	28	28	28	28	28	28	28
Isolation, Inter-band, dB	28	28	28	28	28	28	28
VSWR Return loss, dB	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0
PIM, 3rd Order, 2 x 20 W, dBc	-153	-153	-153	-153	-153	-153	-153
Input Power per Port, maximum, watts	250	250	250	200	200	200	200

Electrical Specifications, BASTA

	698–806	790–894	890–960	1695–1995	1920–2300	2300–2500	2490–2690
Gain by all Beam Tilts, average, dBi	15.8	16.4	16.4	17.8	18.5	18.4	18.7
Gain by all Beam Tilts Tolerance, dB	±0.3	±0.4	±0.5	±0.7	±0.5	±0.5	±0.8

RVV-65B-R3VB-V2

Beamwidth, Horizontal Tolerance, degrees	±2	±1	±5	±5	±4	±4	±5
Beamwidth, Vertical Tolerance, degrees	±0.9	±0.9	±0.5	±0.4	±0.4	±0.3	±0.3
CPR at Boresight, dB	23	27	24	22	25	23	25

Mechanical Specifications

Wind Loading @ Velocity, frontal	535.0 N @ 150 km/h (120.3 lbf @ 150 km/h)
Wind Loading @ Velocity, lateral	290.0 N @ 150 km/h (65.2 lbf @ 150 km/h)
Wind Loading @ Velocity, rear	830.0 N @ 150 km/h (186.6 lbf @ 150 km/h)
Wind Speed, maximum	241 km/h (150 mph)

Packaging and Weights

Width, packed	492 mm 19.37 in
Depth, packed	277 mm 10.906 in
Length, packed	2197 mm 86.496 in
Weight, gross	29.5 kg 65.036 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
UK-ROHS	Compliant

Included Products

BSAMNT-B95-04	-	Wide Profile Antenna Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor top bracket set and one bottom bracket set.
---------------	---	--

* Footnotes

Performance Note	Severe environmental conditions may degrade optimum performance
-------------------------	---

BSAMNT-B95-04



Wide Profile Antenna Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor top bracket set and one bottom bracket set.

Product Classification

Product Type Downtilt mounting kit

General Specifications

Application Outdoor

Color Silver

Dimensions

Compatible Diameter, maximum 115 mm | 4.528 in

Compatible Diameter, minimum 60 mm | 2.362 in

Weight, net 4.5 kg | 9.921 lb

Material Specifications

Material Type Galvanized steel

Packaging and Weights

Included Brackets | Hardware

Packaging quantity 2

Regulatory Compliance/Certifications

Agency

CE
ISO 9001:2015

Classification

Compliant with the relevant CE product directives
Designed, manufactured and/or distributed under this quality management system

