



FACT® Fiber Optic Patch/Splice Panel, 2E high, 96-port, singlemode, loaded with LC/APC Duplex adapters and C-grade pigtails, SMOUV splice tray type, 7.5m indoor Micro-Tube cable, G657A1, yellow jacket, EN50575 CPR Cable EuroClass Dca, right-hand patch

- Designed for use with the all-purpose all-front-access FIST-GR3 fiber frames supporting up to 2,688 LC or 1,344 SC connections in a single frame
- Reduced installation and maintenance time via the toolless snap-on design supporting both interconnect and cross-connect applications
- Flexible customization enabled by 4 chassis types (patch-only, patch-splice, pre-cabled and splice-only) to support all ODF applications
- High density through the single FACT element height (1E) being 30% less tall compared to the industry standard panel height (1HU)

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | Fiber patch panel, with indoor cable |
| Product Brand | FACT® |
| Product Series | FACT |

General Specifications

| | |
|-----------------------------------|---------------------------------------|
| Functionality | Patching |
| Application | Compatible with FIST-GR3-style frames |
| Body Style | Right-hand patch |
| Cable Stub Type | Indoor, microcable |
| Color | Gray |
| Color, front | Gray |
| Growth Configuration | Fully loaded |
| Interface, front | LC/APC |
| Interface, rear | Stub tail |
| Patch Cord Routing | Right sided |
| Patching Capacity, maximum | 96 |
| Rack Type | EIA 19 in |

760254301 | FACT-2ERHPL2S-075CK


| | |
|-----------------------------------|--------------------------------------|
| Rack Units | 1.4 |
| Shelf Movement | Sliding |
| Splicing Capacity, maximum | 96 |
| Splicing Type | SMOUV |
| Total Ports, quantity | 96 |
| Transmission Standards | ETSI EN 300 019-1-3 IEC 61300-3-30 |

Dimensions

| | |
|---------------------|--------------------|
| Height | 61.9 mm 2.437 in |
| Width | 524 mm 20.63 in |
| Depth | 283 mm 11.142 in |
| Cable Length | 7.5 m 24.606 ft |

Ordering Tree

760254301 | FACT-2ERHPL2S-075CK



Optical Specifications

| | |
|--------------------------------|------------------|
| Fiber Mode | Singlemode |
| Fiber Type | G.657.A1 |
| Performance Grade | Standard C grade |
| Insertion Loss, maximum | 0.25 dB |
| Return Loss, minimum | 60 dB |

Environmental Specifications

| | |
|------------------------------------|--------------------------------------|
| Operating Temperature | -40 °C to +70 °C (-40 °F to +158 °F) |
| Storage Temperature | -20 °C to +85 °C (-4 °F to +176 °F) |
| EN50575 CPR Cable EuroClass | Dca |

760254301 | FACT-2ERHPL2S-075CK

Flammability Rating UL 94 V-0

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

* Footnotes

Performance Grade Guarantee to meet IEC 61755-1 Random Mating requirement