


VSRDUALA-TS-B



Adjustable Dual V-Stabilizer™ for a Tower, small leg size (2–8 in)

Product Classification

Product Type Reinforcement kit

General Specifications

Mounting Angle 60°, 203.2 mm (8 in) | Angle 90°, 152.4 mm (6 in) | Straight or tapered legs up to 203.2 mm (8 in) OD

Pipe, quantity 0

Tower Taper Non-tapered | Tapered

Dimensions

Height 990.6 mm | 39 in

Length 1524 mm | 60 in

Mounting Diameter, maximum 203.2 mm | 8 in

Mounting Diameter, minimum 50.8 mm | 2 in

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Clamps | Legs

Packaging quantity 2

Weight, net 49.442 kg | 109 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

