



M-Series Modular Jack, RJ45, Cat6A Unshielded, Red

- Color is more prominently visible across the body of the jack
- Allows for all jack variants to be terminated with the SL termination tool
- Lacing fixture of the SL termination tool is used to establish the cable termination

Product Classification

Regional Availability	North America
Portfolio	Uniprise®
Product Type	Modular jack
Product Series	UNJ Series

General Specifications

ANSI/TIA Category	6A
Cable Type	Unshielded
Color	Red
Conductor Type	Solid Stranded
Integrated Dust Cover Type	None
Mounting	M Series faceplates and panels
Outlet Type	Standard
Termination Tool	SL Termination tool
Termination Type	IDC
Transmission Standards	ANSI/TIA-568.2-D ISO/IEC 11801 Class EA
Wiring	T568A T568B

Dimensions

Panel Cutout, recommended	16.66 x 17.68 mm (0.66 x 0.70 in)
Panel Thickness, recommended	1.6 mm 0.063 in
Height	17.48 mm 0.688 in
Width	16.5 mm 0.65 in
Depth	30.48 mm 1.2 in
Compatible Cable Diameter, maximum	7.24 mm 0.285 in
Compatible Insulated Conductor Diameter, maximum	1.45 mm 0.057 in

760257322 | UNJ10G-RD

Contact Plating Thickness	1.27 µm
Compatible Conductor Gauge, solid	22 AWG 24 AWG
Compatible Conductor Gauge, stranded	24 AWG 26 AWG

Electrical Specifications

Remote Powering	Fully supports the safe delivery of power over LAN cabling described by IEEE 802.3bt (Type 4) and complies with the unmating under electrical load requirements prescribed by IEC 60512-99-002
------------------------	--

PoE Durability	Supports IEEE 802.3bt Type 4 (90 W) applications after 3000 plug to jack mating cycles
-----------------------	--

Material Specifications

Contact Base Material	Beryllium copper
Contact Plating Material	Gold
Material Type	High-impact, flame retardant, thermoplastic PC+ABS Polycarbonate

Mechanical Specifications

Plug to Jack Mating Cycles	Complies to IEC 60603-7 series
-----------------------------------	--------------------------------

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Flammability Rating	UL 94 V-0

Packaging and Weights

Packaging quantity	1
Packaging Type	Bag

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

