

Fiber OSP cable, TeraSPEED® Single Jacket All-Dielectric, Gel-Free, 2 fiber, Stranded Loose Tube, Singlemode G.652.D and G.657.Al, Feet jacket marking, Black jacket color

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

 Portfolio
 CommScope®

 Product Type
 Fiber OSP cable

Product Series D-LN

General Specifications

Cable Type Stranded loose tube

Construction Type Non-armored

Subunit Type Gel-free

Filler, quantity

Jacket Color Black

Jacket Marking Feet

Subunit, quantity 1

Fibers per Subunit, quantity 2


Total Fiber Count 2

**Dimensions** 

Buffer Tube/Subunit Diameter 2.5 mm | 0.098 in Diameter Over Jacket 10.2 mm | 0.402 in

Representative Image





## Material Specifications

Jacket Material PE

## Mechanical Specifications

Minimum Bend Radius, loaded153 mm | 6.024 inMinimum Bend Radius, unloaded102 mm | 4.016 inTensile Load, long term, maximum800 N | 179.847 lbfTensile Load, short term, maximum2700 N | 606.984 lbf

 Compression
 22 N/mm | 125.623 lb/in

 Compression Test Method
 FOTP-41 | IEC 60794-1 E3

Flex 25 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

**Impact** 4.41 N-m | 39.032 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

**Strain** See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

**Vertical Rise, maximum** 1307 m | 4,288.058 ft

Optical Specifications

Fiber Type G.652.D and G.657.A1, TeraSPEED® | OS2



## **Environmental Specifications**

Installation temperature  $-30 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  (-22 °F to +158 °F)

Operating Temperature  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  (-40 °F to +158 °F)

Storage Temperature  $-40 \,^{\circ}\text{C}$  to  $+75 \,^{\circ}\text{C}$  (-40 °F to +167 °F)

Cable Qualification Standards ANSI/ICEA S-87-640 | EN 187105 | Telcordia GR-20

**Environmental Space** Aerial, lashed | Buried

Jacket UV Resistance UV stabilized

Water Penetration 24 h

Water Penetration Test Method FOTP-82 | IEC 60794-1 F5

**Environmental Test Specifications** 

**Cable Freeze** -2 °C ∣ 28.4 °F

Cable Freeze Test Method FOTP-98 | IEC 60794-1 F15

**Heat Age**  $-40 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F})$ 

**Heat Age Test Method** IEC 60794-1 F9

**Low High Bend**  $-30 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \, (-22 \,^{\circ}\text{F to } +140 \,^{\circ}\text{F})$ 

**Low High Bend Test Method** FOTP-37 | IEC 60794-1 E11

**Temperature Cycle**  $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$ 

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 63 kg/km | 42.334 lb/kft

## Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



#### Included Products

CS-8W-LT



Page 3 of 7

 TeraSPEED® G652D/G657A1 Singlemode Fiber

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable



### TeraSPEED® G652D/G657A1 Singlemode Fiber

8.3 µm

## TeraSPEED®

#### **Product Classification**

Portfolio CommScope®

**Product Type** Optical fiber

General Specifications

**Cladding Diameter** 125 μm

**Coating Diameter (Colored)** 249 μm

 Coating/Cladding Concentricity Error, maximum
 12 μm

Core/Clad Offset, maximum 0.5 µm

**Proof Test** 100000 psi | 689.476 N/mm<sup>2</sup>

Dimensions

**Core Diameter** 

Fiber Curl, minimum 4 m | 13.123 ft

Mechanical Specifications

**Macrobending, 20 mm Ø mandrel, 1 turn** 0.75 dB @ 1,550 nm | 1.50 dB @ 1,625 nm

**Macrobending, 30 mm Ø mandrel, 10 turns** 0.25 dB @ 1,550 nm | 1.00 dB @ 1,625 nm

**Macrobending, 60 mm Ø mandrel, 100 turns** 0.05 dB @ 1,550 nm | 0.05 dB @ 1,625 nm

Coating Strip Force, maximum 8.9 N | 2.001 lbf

**COMMSCOPE®** 

## CS-8W-LT

Coating Strip Force, minimum 1.3 N | 0.292 lbf

**Dynamic Fatigue Parameter, minimum** 20

**Optical Specifications** 

Cabled Cutoff Wavelength, maximum1260 nmPoint Defects, maximum0.1 dB

**Zero Dispersion Slope, maximum** 0.092 ps/[km-nm-nm]

Zero Dispersion Wavelength, maximum1324 nmZero Dispersion Wavelength, minimum1300 nm

Optical Specifications, Wavelength Specific

**Attenuation, maximum** 0.22 dB/km @ 1,550 nm | 0.25 dB/km @ 1,490

nm | 0.25 dB/km @ 1,625 nm | 0.36 dB/km @ 1,310

nm | 0.36 dB/km @ 1,385 nm

**Attenuation, typical** 0.19 dB/km @ 1,550 nm | 0.33 dB/km @ 1,310 nm

**Backscatter Coefficient** -79.6 dB @ 1,310 nm | -82.1 dB @ 1,550 nm

**Dispersion, maximum** 18 ps(nm-km) at 1550 nm | 3.5 ps(nm-km) from 1285

nm to 1330 nm at 1310 nm

**Index of Refraction** 1.467 @ 1,310 nm | 1.467 @ 1,385 nm | 1.468 @ 1,550

nm

**Mode Field Diameter** 10.4 μm @ 1,550 nm | 9.2 μm @ 1,310 nm | 9.6 μm @

1,385 nm

**Mode Field Diameter Tolerance**  $\pm 0.4 \, \mu \text{m} \ @ \ 1310 \, \text{nm} \ | \ \pm 0.5 \, \mu \text{m} \ @ \ 1550 \, \text{nm} \ | \ \pm 0.6 \, \mu \text{m}$ 

@ 1385 nm

Polarization Mode Dispersion Link Design Value, maximum 0.04 ps/sgrt(km)

Standards Compliance IEC 60793-2-10, edition 6, model A1a.4 | ITU-T G.652.

D | ITU-T G.657.A1 | TIA-492CAAB (OS2)

**Environmental Specifications** 

Heat Aging, maximum 0.05 dB/km @ 85 °C

 Temperature Dependence, maximum
 0.05 dB/km

 Temperature Humidity Cycling, maximum
 0.05 dB/km

Water Immersion, maximum 0.05 dB/km @ 23 °C

Regulatory Compliance/Certifications

Agency Classification

COMMSCOPE®

# CS-8W-LT

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

### \* Footnotes

**Temperature Dependence, maximum** Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)

Temperature Humidity Cycling, maximum Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F)

up to 95% relative humidity

